



## Pump Module C-601 / C-605

### Reliable solvent delivery

The pump modules C-601 and C-605 are the core components of the BUCHI Sepacore® Chromatography systems. Whatever the application in isocratic or gradient mode is, the modules provide a reproducible and pulse free flow rate.



#### Universal

Pump any solvent at low or medium pressure



#### Small and powerful

Smallest footprint with broad flow rate range and gradient capability



#### Flexible

Upgradeable according to your application and budget



## C-601 / C-605: Your most important benefits



### Universal

- Free choice of solvents thanks to inert pump head material
- Reliable flow rate up to 50 bar
- Multiple control modes according to the application



### Small and powerful

- Smallest footprint with flow rate up to 250 mL/min
- Pulse free solvent delivery using a 3-piston pump head
- Plug and play portable unit



### Flexible

- Configuration adjusted to your needs and budget
- Easily upgradeable: isocratic to gradient or manual to computer control

## Complete your portfolio



Fraction collector  
C-660  
Fraction collection



FlashPure  
Cartridges  
Get the most out of  
your flash purifications



UV-Vis Detector  
C-640  
UV-Vis detection



SepacoreControl  
Software  
Full control software

