A. POLOK - KOWALSKA, S. KOWALSKI 44-300 WODZISŁAW ŚLĄSKI, UL. KOKOSZYCKA 172 C

Data sheet

Climatic Chamber with Phytotron System

KK 400 FIT P Smart PRO



The photo above is for reference only, may show additional options not included in standard equipment. The real appearance, particularly color and structure of the material may differ from the ones presented in the photo.

Advantages of the SMART PRO controller:

- large (7"), clear, full colour touch screen
- LAN, USB ports and WiFi for communication and data transfer
- multi-segment time and temperature programs
- overview of data in tabular and graphic form
- visual and sound alarm
- Admin function for management
- password protected log-in
 internal memory for programs and data storage
- event registry with user notifications
- LabDesk software and user manual for direct download




Smart PRO - preview screen





A. POLOK – KOWALSKA, S. KOWALSKI 44-300 WODZISŁAW ŚLĄSKI, UL. KOKOSZYCKA 172 C

TECHNICAL DATA	
air convection	forced
chamber capacity [l]	416
working capacity [l]	390
controller	microprocessor PID
display	7" full colour touch screen
TEMPERATURE AND HUMIDITY	
temperature range [°C]	0+60 (with light on +10+50)
temperature resolution every [°C]	0,1
temperature variation at 25°C and 60%rH [+/-°C]*	2,0
relative humidity range [%]	3090 (see chart for details)
humidity resolution every [%]	1,0
humidity variation at 25°C and 60% rH [%rH]	5,0
over temperature protection	class 3.3 to DIN 12880



tel. (+48) 32 453 91 70

obszar pracy krótkotrwałej (max.24 h) short-term work area (max. 24h)

Wilgotność względna / Relative humidity [%]

CHAMBER	
door	double (external solid, internal glass) / external glass (option)
interior	
Smart PRO	acid-proof stainless steel to DIN 1.4301
IG Smart PRO	acid-proof stainless steel to DIN 1.4301
housing	
Smart PRO	powder coated sheet
IG Smart PRO	stainless steel linen finish








overall dims [mm] /1/	
A width	1020
B height	1850
depth C	1000
internal dims [mm]	
width D	800
height E	1040
depth F	500

tel. (+48) 32 453 91 70



shelves (standard max)	3 14
max shelf workload [kg] /2/	10
- reinforced shelf version (PW) [kg] /3/	100
max unit workload [kg]	120
weight [kg]	185
ELECTRICAL PARAMETERS	
power supply	230V 50-60Hz
nominal power [W]	2550
refrigerant	R290 / GWP=3
warranty	24 months

POL-EKO-APARATURA

all the above technical data refer to standard units (without optional accessories)

- * variation (K) calculated for chamber as: K= +/- (T average max. T average min.) / 2
- ** other power supplies on request
- 1 depth doesn't include 50 mm of power cable
- 2 on uniformly loaded surface
- 3 reinforced shelf

manufacturer

4 - reinforced version

OPTIONS AND ACCESSORIES



Order number: */A

Door with viewing window



Order number: */P INOX

Stainless steel wire shelf INOX



Order number: */PP

Perforated shelf





A. POLOK – KOWALSKA, S. KOWALSKI 44-300 WODZISŁAW ŚLĄSKI, UL. KOKOSZYCKA 172 C

	Order number: */PW	Reinforced shelf
	Order number: KUW GN*/*	Stainless steel cuvettes
90% 30%	Order number: FIT/R3	FIT panels independent control
	Order number: GNZ	Internal socket
(((((Order number: KK/CP	Low water level sensor
>0<	Order number: BRT/*/L or IQ/OQ/PQ	Calibration and IQ, OQ, PQ qualification
4	Order number: BPP 12	Battery backup for display
ALARM	Order number: PORT ALARM	Dry alarm contact
USB	Order number: USBK	USB cable
LAN	Order number: LANK	LAN cable
20mm	Order number: OCZ/20	Non-standard access port 20 mm
30mm	Order number: OCZ/30	Additional access port 30 mm
60mm	Order number: OCZ/60	Non-standard access port 60 mm
100mm	Order number: OCZ/100	Non-standard access port 100 mm
H20	Order number: KK/Z	Container for deionised water



Order number: KK/Z

[]





Want to know more?

If you have questions about this item, please give us a call on 01257 270 433.

Richmond Scientific are a family run business in Lancashire. We're a small team, and we're always just a phone call away. With over 30 years in the business there's not much we haven't seen before, and we're always happy to chat.

Have kit to sell?

Call us on 01257 270 433 Email: harry@richmondscientific.com Visit: www.richmondscientific.com

Visit Website Sell used kit Our newsletter